


electrical connection box VAVE-L1-1VR1-LP

Part number: 573921

FESTO



Data sheet

Feature	Value
Polarity protected	Bipolar
Additional functions	Spark arresting
Signal status display	LED
Nominal operating voltage DC	24 V 12 V
Surge strength	0.8 kV
Degree of contamination	3
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Protection class	IP65
Ambient temperature	-5 ... 60 °C
Assembly position	Any
Max. tightening torque	0.27 Nm
Product weight	3.2 g
Electrical connection	4-pin/2-pin M8 / - Plug / socket
Protective earth connection	Not available
Mounting type	On solenoid valve with self-tapping screw
Housing colour	Black
Materials note	Conforms to RoHS
Material cover	PA
Material seals	EPDM
Material housing	PA
Material screws	Heat-treatment steel