

time delay valve



VZO-3-PK-3

Part number: 5754

FESTO

Normally open, on 2n sub-base with barbed fitting connection for 3mm ID tubing.

Longer delays can be obtained by connecting an additional reservoir to the valve.



Data sheet

Feature	Value
Nominal size	2 mm
Type of actuation	pneumatic
Design structure	Poppet valve with spring return
Overlap	Underlap
Note on forced dynamisation	Switching frequency at least once a week
Operating pressure	2.5 ... 8 bar
Standard nominal flow rate	60 l/min
Adjustable delay times	0.25 ... 5 s
Pause period for reset	≥ 50 ms
Repetition accuracy, time setting	$\pm 0,5$ s
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
PWIS conformity	VDMA24364-B1/B2-L
Pilot medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Ambient temperature	-10 ... 60 °C
Product weight	150 g
Mounting type	Front panel installation On mounting frame Optional
Pneumatic connection	PK-3
Material housing	Zinc die-casting