

common supply manifold VABM-B10-20-N38-6-P53

Part number: 576379

FESTO



Data sheet

Feature	Value
Grid dimension	22 mm
Mounting position	optional
Max. number of valve positions	6
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	395 g
Type of mounting	Via mounting bracket
Pneumatic connection, port 1	3/8 NPT
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy