


sub-base VMPAC-AP-14-1

Part number: 576572

FESTO



Data sheet

| Feature | Value |
|---|--------------------------------|
| Width | 32.8 mm |
| Length | 169 mm |
| Grid dimension | 26.8 mm |
| Max. number of valve positions | 1 |
| Operating pressure | -0.9 ... 8 bar |
| Pilot pressure | 3 ... 8 bar |
| Corrosion resistance classification CRC | 4 - Very high corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| Ambient temperature | -5 ... 50 °C |
| Product weight | 160 g |
| Pneumatic connection, port 2 | G1/4 |
| Pneumatic connection, port 4 | G1/4 |
| Materials note | Conforms to RoHS |
| Material housing | PA-reinforced |