

**LFRN-1/4-B****Filter regulator**

<b>Feature</b>	<b>Data/description</b>
Design structure	Filter regulator with pressure gauge
Ambient temperature	-10 - 60 °C
Mounting type	with through hole with accessories Optional
Medium temperature	-10,0 - 60,0 °C
Operating medium	Compressed air
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Pressure gauge	with pressure gauge
Inlet pressure 1	0,000 - 10,000 bar
Grade of filtration	8,000 µm
Condensate drain	manual rotary
Pressure control range	0,100 - 1,600 bar
Max. condensate volume	75,000 cm <sup>3</sup>