


T quick connector TCK-1/4-PK-6-KU

Part number: 6266

FESTO



Data sheet

| Feature | Value |
|-----------------------------------------------|--------------------------------------------------------------------------------------------|
| Nominal size | 5.3 mm |
| Type of seal on screwed plug | Sealing edge |
| Mounting position | optional |
| Design | T-shape |
| Size of pack | 10 |
| Operating pressure complete temperature range | -0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C...60 °C |
| Pneumatic connection, port 1 | Male thread G1/4 |
| Pneumatic connection, port 2 | For tubing outside diameter of 8 mm For barbed fitting inside diameter of 6 mm with nut |
| Material union nut | POM |
| Note on materials | RoHS-compliant |
| Material housing | POM |
| Material hollow bolt | Wrought aluminium alloy, anodised |
| Material swivel fitting | POM |