

Pressure regulator LR-1/8-D-7-I-MINI-MPA

Part number: 8002389

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Mini |
| Series | D |
| Actuator lock | Rotary knob with detent |
| Mounting position | optional |
| Design | Directly actuated diaphragm regulator |
| Controller function | Output pressure constant Via primary pressure compensation With secondary venting With return flow function |
| Pressure gauge (ANALOG) or Pressure display (DIGITAL) | With pressure gauge |
| Operating pressure | 1 bar...16 bar |
| Pressure regulation range | 0.5 bar...7 bar |
| Max. pressure hysteresis | 0.2 bar |
| Standard nominal flow rate | 1000 l/min |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Air purity class at output | Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases |
| Media temperature | -10 °C...60 °C |
| Ambient temperature | -10 °C...60 °C |
| Product weight | 350 g |
| Type of mounting | Front panel mounting In-line installation With accessories |
| Pneumatic connection, port 1 | G1/8 |
| Pneumatic connection, port 2 | G1/8 |
| Note on materials | RoHS-compliant |
| Material sub-base | Die-cast zinc |
| Material seals | NBR |

| Feature | Value |
|------------------|---------------|
| Material housing | Die-cast zinc |