


Flow control VFFG-T-M5-15

Part number: 8025715

FESTO



Data sheet

Feature	Value
Valve function	Flow control function
Type of mounting	Via thread
Standard nominal flow rate in flow control direction	67.4 l/min
Operating pressure	-0.9 bar...10 bar
Ambient temperature	-5 °C...60 °C
Nominal size	1.55 mm
b value	0.5
C value	0.25 l/sbar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C...60 °C
Product weight	0.5 g
Note on materials	RoHS-compliant
Material hollow bolt	PA