


# common supply manifold VABM-B10-25-G12-5-P53

Part number: 8026222

FESTO



## Data sheet

| Feature                        | Value                         |
|--------------------------------|-------------------------------|
| Grid dimension                 | 27.5 mm                       |
| Mounting position              | optional                      |
| Max. number of valve positions | 5                             |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L             |
| Product weight                 | 504 g                         |
| Type of mounting               | Via mounting bracket          |
| Pneumatic connection, port 1   | G1/2                          |
| Note on materials              | RoHS-compliant                |
| Material manifold rail         | Wrought aluminium alloy       |