

supply manifold

VABM-B10-25-N12-5-P53

Part number: 8026231

FESTO



Data sheet

| Feature | Value |
|---|-------------------------------|
| Grid dimension | 27.5 mm |
| Assembly position | Any |
| Max. number of valve positions | 5 |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Product weight | 504 g |
| Mounting type | With mounting bracket |
| Pneumatic connection, port 1 | 1/2 NPT |
| Materials note | Conforms to RoHS |
| Material manifold | Wrought Aluminium alloy |