

Reducing nipple NPFC-R-G18-M5-MF

Part number: 8030307

FESTO



Data sheet

| Feature | Value |
|--------------------------------|--|
| Material threaded fitting | Nickel-plated brass |
| Size of pack | 10 |
| Operating pressure | -0.95 bar...50 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [-::-] |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C...150 °C |
| Product weight | 8.2 g |
| Pneumatic connection, port 1 | G1/8 |
| Pneumatic connection, port 2 | M5 |
| Note on materials | RoHS-compliant |