


sub-base VABS-K1-7B-12-U14-P

Part number: 8047063

FESTO



Data sheet

| Feature | Value |
|---|---|
| Nominal size | 1.2 mm |
| Valve size | 7 mm |
| Fluid connection | Female thread 1/4-28 UNF-2B |
| Assembly position | Any |
| Design structure | Connection direction underneath |
| Flow direction | reversible |
| Operating medium | Fluid media Gaseous media |
| Note on operating and pilot medium | Observe resistance of materials that come into contact with media |
| Corrosion resistance classification CRC | 0 - No corrosion stress |
| PWIS conformity | VDMA24364 zone III |
| Storage temperature | -20 ... 70 °C |
| Food-safe | See Supplementary material information |
| Medium temperature | 0 ... 50 °C |
| Ambient temperature | 0 ... 50 °C |
| Max. tightening torque, valve mounting | 0.15 Nm |
| Max. tightening torque for fitting | 0.6 Nm |
| Product weight | 3 g |
| Mounting method for sub-base | with through hole |
| Mounting method for valve | with internal (female) thread |
| Materials note | Conforms to RoHS |
| Material of connecting plate | PEEK |
| Material threaded sleeve | High alloy steel, non-corrosive |