

Common supply manifold OABM-P-G3-15-8

Part number: 8049146

FESTO



Data sheet

| Feature | Value |
|--------------------------------|-------------------------------|
| Number of device positions | 8 |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Max. tightening torque | 3.3 Nm |
| Min. tightening torque | 0.3 Nm |
| Product weight | 172 g |
| Type of mounting | With through-hole |
| Pneumatic connection, port 1 | G1/8 |
| Note on materials | RoHS-compliant |
| Material sub-base | Wrought aluminium alloy |