

Parallel kit EAMM-U-70-D32-68GA-96

Part number: 8058951

FESTO



Data sheet

Feature	Value
Size	70
Mounting position	optional
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	118 kgmm ²
Frictional torque independent of load	0.18 Nm
Transmittable torque	7 Nm
Product weight	1800 g
Interface code, actuator	D32
Interface code, motor in	68GA
Note on materials	RoHS-compliant