

parallel kit EAMM-U-70-D50-60RA-96

Part number: 8058963

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Size	70
Assembly position	Any
Max. speed	5,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	118 kgmm ²
No-load driving torque	0.18 Nm
Transferable torque	7 Nm
Product weight	1,800 g
Interface code, actuator	D50
Interface code, motor in	60RA
Materials note	Conforms to RoHS