

Quick coupling plug NPHS-S6-M-G38

Part number: 8059259

FESTO



Data sheet

Feature	Value
Nominal size	7.85 mm
Operating pressure complete temperature range	-0.95 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Nominal torque	12.5 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	27 g
Pneumatic connection, port 1	Male thread G3/8
Note on materials	RoHS-compliant