


axial kit EAMM-A-L95-160G

Part number: 8063532

FESTO



Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	192 Nm
Product weight	5,826 g
Interface code, actuator	L95
Interface code, motor in	160G
Materials note	Conforms to RoHS