


Axial kit EAMM-A-M80-90GA

Part number: 8063568

FESTO



Data sheet

Feature	Value
Mounting position	optional
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Transmittable torque	60 Nm
Product weight	1332 g
Interface code, actuator	M80
Interface code, motor in	90GA
Note on materials	RoHS-compliant