


# axial kit EAMM-A-N48-90GA

Part number: 8063603

FESTO



## Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	17 Nm
Product weight	1,348 g
Interface code, actuator	N48
Interface code, motor in	90GA
Materials note	Conforms to RoHS