

Coupling EAMD-32-32-14-16X20-U

Part number: 8086051

FESTO



Data sheet

| Feature | Value |
|------------------------|------------------------|
| Mounting diameter 1 | 14 mm |
| Mounting diameter 2 | 16 mm |
| Size | 32 |
| Nominal length | 32 mm |
| Mounting position | optional |
| Max. rotational speed | 8000 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C...60 °C |
| Relative air humidity | 0 - 95% |
| Ambient temperature | -25 °C...60 °C |
| Mass moment of inertia | 14.5 kgmm ² |
| Transmittable torque | 16 Nm |
| Product weight | 124 g |
| Note on materials | RoHS-compliant |