


parallel kit EAMM-U-65-T42-60PA-87

Part number: 8091225

FESTO



Data sheet

Feature	Value
Size	65
Centre-to-centre distance	87 mm
Assembly position	Any
Gear unit ratio	1:1
Max. speed	3,000 1/min
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	0 ... 50 °C
Mass moment of inertia	41.2 kgmm ²
No-load driving torque	0.22 Nm
Transferable torque	3 Nm
Product weight	600 g
Interface code, actuator	T42
Interface code, motor in	60PA
Materials note	Conforms to RoHS