


sub-base VABS-P16-10S-M5

Part number: 8097804

FESTO



Data sheet

Feature	Value
Width	26 mm
Assembly position	Any
Special characteristics	Oxygen-compatible to DIN EN 1797
Max. number of valve positions	1
Operating pressure	0 ... 7 bar
Operating medium	Compressed air to ISO 8573-1:2010 [6:3:4] Inert gases Air Oxygen Nitrogen
Note on operating and pilot medium	Lubricated operation not possible Maximum particle size: 5 µm
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Storage temperature	-20 ... 70 °C
Medium temperature	-10 ... 60 °C
Relative air humidity	0 - 60 % non-condensing
Ambient temperature	-10 ... 60 °C
Product weight	25 g
Mounting type	with through hole with internal (female) thread
Pneumatic connection, port 1	M5
Pneumatic connection, port 2	M5
Materials note	Conforms to RoHS
Material of connecting plate	Wrought Aluminium alloy