

Blanking plug B-M7-F1A

Part number: 8144525

FESTO



Data sheet

Feature	Value
Size of pack	10
Variants	Metals with copper, zinc or nickel as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 6 according to ISO 14644-1
Nominal torque	1.5 Nm
Tolerance for nominal tightening torque	± 15%
Product weight	2 g
Type of mounting	Internal hexagon, size 3 mm
Pneumatic connection, port 1	Male thread M7
Note on materials	RoHS-compliant
Material blanking plug	Steel, nickel-plated
Material o-ring	Stainless steel NBR