


Axial kit EAMM-A-N80-150A

Part number: 8157277

FESTO



Data sheet

Feature	Value
Mounting position	optional
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Transmittable torque	47 Nm
Product weight	2407 g
Interface code, actuator	N80
Interface code, motor in	140A 150A
Note on materials	RoHS-compliant