

Plastic-coated metal tube PM-6

Part number: 9087

FESTO



Data sheet

Feature	Value
Outside diameter	8 mm
Flow-relevant bending radius	25 mm
Inside diameter	5.2 mm
Temperature-dependent operating pressure	-0.95 bar...30 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7::-:]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-29 °C...65 °C
Product weight according to length	0.032 kg/m
Colour	Black
Note on materials	RoHS-compliant
Material tubing	Wrought aluminium alloy PE