


bulkhead quick connector SCK-PK-3

Part number: 9420

FESTO

Metal version.



Data sheet

Feature	Value
Nominal size	2.4 mm
Assembly position	Any
Design	Bulkhead
Container size	10
Operating pressure for entire temperature range	-0.095 ... 1 MPa
Operating pressure complete temperature range	-0.95 ... 10 bar
Operating pressure for entire temperature range	-13.775 ... 145 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Pneumatic connection, port 1	For tubing outside diameter 4 mm for barbed connector internal diameter 3 mm with nut
Pneumatic connection, port 2	For tubing outside diameter 4 mm for barbed connector internal diameter 3 mm with nut
Material of union nut	Anodised wrought aluminium alloy
Materials note	Conforms to RoHS
Material nut	steel, galvanized
Material – connector	Anodised wrought aluminium alloy