

Double nipple E-G1/8-1/8NPT

Part number: 9630

FESTO



Data sheet

Feature	Value
Nominal size	5.95 mm
Operating pressure complete temperature range	-0.95 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Max. tightening torque pneumatic connection 1	6 Nm
Max. tightening torque pneumatic connection 2	7 Nm
Nominal torque	10.55 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	9.1 g
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	1/8 NPT
Note on materials	RoHS-compliant