


Short pulse valve VLK-3-PK-3

Part number: 9639

FESTO



Data sheet

| Feature | Value |
|----------------------------|--|
| Nominal size | 2.5 mm |
| Operating pressure | 2.5 bar...8 bar |
| Standard nominal flow rate | 90 l/min |
| Explosion protection | The information in the certificate must be observed! Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C...60 °C |
| Product weight | 170 g |
| Type of mounting | On mounting frame |
| Material seals | TPE-U(PU) |
| Material housing | Die-cast zinc |