


Pneumatic limit valve RWN/O-3-1/8-B

Part number: 9694

FESTO



Data sheet

Feature	Value
Valve function	3/2-way, monostable, open/closed
Standard nominal flow rate	120 l/min
pneumatic working port	G1/8
Operating pressure	-0.95 bar...8 bar
LABS (PWIS) conformity	VDMA24364-B2-L