

Indicating plug MFL-230AC

Part number: 10005

FESTO

With light-emitting diode(LED)



Data sheet

Feature	Value
Product weight	14 g
Electrical connection	Plug pattern type B to EN 175301-803 to industry standard (11 mm)
Nominal operating voltage, AC	230 V
Line frequency	50 ... 60 Hz
Permissible voltage fluctuation	-20 % / +15 %
Protection class	IP65 to IEC 60529
Ambient temperature	-20 ... 60 °C
CE symbol (see declaration of conformity)	according to EU low voltage guideline
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
PWIS conformity	VDMA24364-B2-L
Material housing	PA6 reinforced