


# Axial kit EAMM-A-D19-28A

Part number: 1081659

FESTO

Suitable for electric drives.



## Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364 zone III
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	1.1 Nm
Product weight	80 g
Interface code, actuator	D19A
Interface code, motor in	28A
Materials note	Conforms to RoHS