



Shock absorber DYSR-20-25-Y5-T

Part number: 1138647

FESTO



Data sheet

Feature	Value
Size	20
Stroke	25 mm
Cushioning	adjustable
Assembly position	Any
Position detection	No
Max. impact speed	3 m/s
Reset time short	0.3 s
Reset time long	3 s
Mode of operation	single-acting pushing action
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-10 ... 80 °C
Cushioning length	25 mm
Max. stop force	2,500 N
Max. energy consumption per stroke	62.5 J
Max. energy consumption per hour	135,000 J
Max. residual energy	0.32 J
Reset force	9 N
Product weight	425 g
Mounting type	with lock nut
Materials note	Conforms to RoHS
Material seals	NBR
Material housing	steel, galvanized
Material piston rod	High alloy steel, hardened