



Solenoid valve

MVH-5-1/8-L-S-B-VI

Part number: 117425

FESTO

With solenoid coil and manual override, without socket.
This type is suitable for vacuum.



Data sheet

Feature	Value
Valve function	5/2 single solenoid
Working pressure	-0.9 ... 10 bar
Pilot pressure	3 ... 10 bar
Operating medium	filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated Vacuum
Pilot medium	filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated
Pilot air port 12	G1/8
Pneumatic connection, port 1	G1/8
Pneumatic connection, 11	G1/8
Materials note	Contains PWIS substances