

# Plastic tubing

## PU-9-SW

Part number: 12134

FESTO

For CN and CK connectors, particularly flexible and kink-resistant, polyurethane (not approved for use in the food industry).  
The maximum pressure value is permissible at the maximum temperature.



## Data sheet

Feature	Value
Outside diameter	11.6 mm
Bending radius relevant for flow rate	76 mm
Inside diameter	9 mm
Operating pressure complete temperature range	0 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-35 ... 60 °C
Product weight according to length	0.056 kg/m
Pneumatic connection	for barbed connector internal diameter 9 mm with nut
Color	Black
Shore hardness	A 91 +/-3
Materials note	Conforms to RoHS
Material tubing	TPE-U(PU)