

# Plastic tubing PUN-CM-12-SW

Part number: 130818

FESTO

Standard O.D tubing, for QS plug connectors, polyurethane (not approved for use in the food industry). Antistatic.



## Data sheet

Feature	Value
Outside diameter	12 mm
Bending radius relevant for flow rate	70 mm
Inside diameter	8 mm
Min. bending radius	30 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 ... 1 MPa
Temperature dependent working pressure	-0.95 ... 10 bar
Temperature-dependent operating pressure	-13.775 ... 145 psi
Surface resistance	0.01 ... 10 MOhm
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-35 ... 60 °C
Product weight according to length	0.08107 kg/m
Pneumatic connection	For push-in connector outside diameter 12 mm
Color	Black
Shore hardness	D 52 +/-3
Materials note	Conforms to RoHS
Material tubing	TPE-U(PU)