

Clamping sleeve EAMH-50-8-C13.6-P

Part number: 1354094

FESTO



Data sheet

Feature	Value
Size	50
Assembly position	Any
Max. speed	6,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	0.35 kgmm ²
Product weight	16 g
Materials note	Conforms to RoHS