

# Clamping sleeve EAMH-110-25-C34-P

Part number: 1354107

FESTO



## Data sheet

Feature	Value
Size	110
Assembly position	Any
Max. speed	5,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	25.8 kgmm <sup>2</sup>
Product weight	170 g
Materials note	Conforms to RoHS