


# Illuminating seal MV-LD-230

Part number: 151716

FESTO

For MV-valves.



## Data sheet

Feature	Value
Switching position indicator	LED
Mounting type	On solenoid valve with M3 central screw
Product weight	1.6 g
Electrical connection	Rectangular design, MSV Per DIN EN 175301-803 Design B
Nominal operating voltage, AC	230 V
Surge strength	2.5 kV
Protective earth connection	Available
Nominal power, illuminating seal	0.33 W
Permissible voltage fluctuation	+/- 10 %
Protection class	IP65
Ambient temperature	-25 ... 85 °C
CE symbol (see declaration of conformity)	according to EU low voltage guideline
Degree of contamination	3
Materials information, housing	TPE-U(PU)