



Linear actuator DGO-32- -PPV-A-B

Part number: 15225

FESTO

For proximity sensing, with magnetic coupling.



Data sheet

Feature	Value
Stroke	10 ... 3,500 mm
Piston diameter	32 mm
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Assembly position	Any
Driver principle	force-locking (magnet)
Position detection	For proximity sensor
Working pressure	1.4 ... 7 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-20 ... 60 °C
Cushioning length	20 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	483 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	483 N
Additional mass factor per 10 mm of stroke	6 g
Basic weight for 0 mm stroke	2,400 g
Pneumatic connection	G1/8
Material cover	Aluminum
Material seals	NBR TPE-U(PU)
Material housing	High alloy steel