

Push-in bulkhead connector QSS-8

Part number: 153159

★ Core product range

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal size	7 mm
Assembly position	Any
Design	Bulkhead
Container size	10
Design structure	Push/pull principle
Operating pressure for entire temperature range	-0.095 ... 0.6 MPa
Operating pressure complete temperature range	-0.95 ... 6 bar
Operating pressure for entire temperature range	-13.775 ... 87 psi
Temperature-dependent operating pressure	-0.095 ... 1.4 MPa
Temperature dependent working pressure	-0.95 ... 14 bar
Temperature-dependent operating pressure	-13.775 ... 203 psi
Maritime classification	see certificate
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 80 °C
Product weight	19 g
Mounting type	External hexagon A/F 19
Pneumatic connection, port 1	For tubing outside diameter 8 mm
Pneumatic connection, port 2	For tubing outside diameter 8 mm
color of release ring	blue
Materials note	Conforms to RoHS
Material housing	Anodised aluminium
Material release ring	POM
Material nut	Nickel-plated brass
Material of tubing seal	NBR
Material of tube retaining claw	High alloy steel, non-corrosive