

Push-in bulkhead connector QSS-3/8T-U

Part number: 153765

FESTO

This product is only available if ordered from the Festo Corporation, USA.
Type to be discontinued. Available until 2011.



Data sheet

| Feature | Value |
|---|-----------------------------------|
| Size | Standard |
| Nominal size | 6.7 mm |
| Assembly position | Any |
| Container size | 1 |
| Design structure | Push/pull principle |
| Working pressure | -0.95 ... 10 bar |
| Temperature dependent working pressure | -0.95 ... 10 bar |
| Operating medium | Filtered compressed air Vacuum |
| Corrosion resistance classification CRC | 1 |
| Ambient temperature | -10 ... 60 °C |
| Authorization | Germanischer Lloyd |
| Pneumatic connection | for tubing, 3/8" outside diameter |
| color of release ring | Grey |
| Materials note | Conforms to RoHS |
| Materials information, housing | Brass Nickel plated |
| Release ring material data | POM |
| Materials information for tubing seal | NBR |
| Hose clamping segment material data | High alloy steel, non-corrosive |