



# Round cylinder EG-4-15-PK-2

Part number: 15887

FESTO

Micro Pneumatic series



## Data sheet

Feature	Value
Stroke	15 mm
Piston diameter	4 mm
Cushioning	No cushioning
Assembly position	Any
Design structure	Piston Piston rod Cylinder barrel
Position detection	No
Variants	Single-ended piston rod
Working pressure	3.5 ... 7 bar
Mode of operation	single-acting pushing action
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	5 ... 60 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	4.9 N
Theoretical minimum spring return force	1.8 N
Theoretical maximum spring return force	2.6 N
Product weight	5 g
Mounting type	with lock nut
Pneumatic connection	PK-2
Materials note	Conforms to RoHS
Material cover	High alloy steel
Material seals	TPE-U(PU)
Material piston rod	High alloy steel
Material cylinder barrel	Nickel-plated brass