

Flange mounting CRFBN-20/25

Part number: 161865

FESTO



Data sheet

Feature	Value
Size	20/25
Mounting position	Any
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-40 °C...150 °C
Product weight	52 g
Note on materials	RoHS-compliant
Mounting material	High-alloy stainless steel