

Compressed air filter LF-3/8-D-MINI-A

Part number: 162608

FESTO



Data sheet

Feature	Value
Size	Mini
Series	D
Mounting position	Vertical +/- 5°
Grade of filtration	40 µm
Condensate drain	Fully automatic
Structural design	Sinter filter with centrifugal separator
Max. condensate volume	22 cm ³
Bowl guard	Metal bowl guard
Operating pressure	2 bar...12 bar
Standard nominal flow rate	1400 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:9:-] Inert gas
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:8:4] Inert gas
Temperature of medium	5 °C...60 °C
Ambient temperature	5 °C...60 °C
Product weight	250 g
Type of mounting	Line installation With accessories
Pneumatic connection 1	G3/8
Pneumatic connection 2	G3/8
Note on materials	RoHS-compliant
Compressed air filter material	PE
Housing material	Die-cast zinc
Material of bowl	PC