

Quick coupling EAMC-42-50-9-12

Part number: 1732001

FESTO



Data sheet

| Feature | Value |
|------------------------|------------------------|
| Diameter of holder 1 | 9 mm |
| Diameter of holder 2 | 12 mm |
| Size | 42 |
| Nominal length | 50 mm |
| Mounting position | Any |
| Max. rotational speed | 6000 1/min |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C...60 °C |
| Relative air humidity | 0 - 95 % |
| Ambient temperature | -25 °C...60 °C |
| Mass moment of inertia | 34.8 kgmm ² |
| Transferable torque | 17 Nm |
| Product weight | 146 g |
| Note on materials | RoHS-compliant |