



# Proximity Sensor

## SMT-10-PS-KL-LED-24

Part number: 173218

FESTO

Electrical, contactless, PNP, for actuators with 10 mm sensor slot, with cable.



## Data sheet

Feature	Value
Design	for round slot
Conforms to standard	EN 60947-5-2
Authorization	C-Tick
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Materials note	Free of copper and PTFE
Measuring principle	Magnetostrictive
Ambient temperature	-20 ... 60 °C
Switch output	PNP
Switching element function	Normally open contact
Reproducibility of switching value	+/- 0,1 mm
Switch-on time	≤ 0.2 ms
Switch-off time	≤ 0.2 ms
Max. output current	200 mA
Max. contact rating DC	6 W
Voltage drop	1.7 V
Residual current	≤ 0.01 mA
Short circuit strength	Pulsing
Overload withstand capability	Available
Operating voltage range DC	10 ... 30 V
Polarity protected	for all electrical connections
Electrical connection	Cable 3-core
Connector exit direction	axial
Cable length	2.5 m
Materials information, cable sheaths	PUR
Mounting type	Clamped in round slot Insertable into slot lengthwise
Tightening torque	0.05 ... 0.1 Nm
Product weight	20 g
Materials information, housing	Nickel plated Brass PA High alloy steel, non-corrosive
Operating status display	Yellow LED
Ambient temperature	-5 ... 60 °C
Protection class	IP65 IP67
Insulation voltage	50 V
Degree of contamination	3