


Clevis flange SNCB-125

Part number: 174396

FESTO



Data sheet

Feature	Value
Size	125
Based on norm	ISO 15552
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% copper by mass are excluded from use. Exception are printed circuit boards, cables, electrical connectors and coils
Ambient temperature	-40 °C...90 °C
Product weight	1860 g
Note on materials	RoHS-compliant
Mounting material	Die-cast aluminum
Bolt material	Steel, galvanized
Material of bearing	Polymer
Disc material	Steel, galvanized
Material of screws	Steel, galvanized
Fuse material	Spring steel, galvanized