

Mounting kit SMBR-8-63

Part number: 175100

FESTO



Data sheet

Feature	Value
Size	63
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-20 °C...70 °C
Profile material	Wrought aluminum alloy
Note on materials	RoHS-compliant
Retaining bracket material	POM