

Connecting cable KM8-M8-GSGD-1

Part number: 175489

FESTO

for inputs, 1 m long, with straight plug and straight socket



Data sheet

Feature	Value
Operating voltage range AC	≤ 60 V
Operating voltage range DC	≤ 75 V
Permissible current load	4 A
Protection class	IP65
Ambient temperature	-25 ... 85 °C
Electrical connection	Plug straight / socket straight M8x1 / M8x1 3-pin / 3-pin
Cable structure	3x0,25
Cable length	1 m
Cable sheath color	Grey
Materials information, cable sheaths	PUR