



Round cylinder DSAG-50- -PPV-S6

Part number: 176550

FESTO

End cap with threaded lug, with heat-resistant seals up to 120 °C
This product is only available if ordered from Festo Korea Co. Ltd.



Exemplary representation

Data sheet

Feature	Value
Stroke	1 ... 500 mm
Piston diameter	50 mm
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Working pressure	1 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Ambient temperature	-20 ... 120 °C
Cushioning length	27 mm
Theoretical force at 6 bar, return stroke	989 N
Theoretical force at 6 bar, advance stroke	1,178 N
Moving mass with 0 mm stroke	892 g
Additional weight per 10 mm stroke	40.1 g
Basic weight for 0 mm stroke	977 g
Additional mass factor per 10 mm of stroke	24.8 g
Pneumatic connection	M45x1,5
Materials information for cover	Wrought Aluminum alloy
Materials information for seals	FPM
Materials information, housing	High alloy steel, non-corrosive
Materials information for piston rod	High alloy steel